



CX FM

The modular inserts must be installed in suitable frames, which are then mounted in traditional enclosures or in COB panel supports.
Alternatively, individual modules with a width of 14,7 mm can be installed in plastic supports.

frames for modular units

page:
316

dummy module




description	part No.
-------------	----------

dummy module for unused frame seats

CX FM

Remark:
The new version is formed by a single piece and has a reduced height.
It allows the mating of a MIXO insert including it with a corresponding MIXO insert even having - in front of the dummy module - a regular male or female module equipped with contacts, which obviously will not work. The sole exceptions to this feature are that an insert with this dummy module cannot mate an insert showing in front a CX 3/4 XDF/M, CX 04 XF/M or CX 02 HF module.



- 1 frame slot